6622A Series



DIRECT CURRENT COMPARATOR RESISTANCE BRIDGES

World's First One Bridge Family of Modular and Expandable DCC Bridges



6622A Series Features

- Widest Available Range from 1 m Ω ~1 G Ω
- Modular Design, Expandable Capabilities, Complete Investment Protection
- Full 10.5 Digits (0.1 ppb) Display Resolution
- Unique Measurement Trending Display
- Provides Measurement Results on Display
- Change All Key parameters "on-the-fly" while the measurement is running
- Built-In Voltages to 1000 Vdc
- Linearity: ± 0.01 ppm of Full Scale
- Resolution: ± 0.0001 ppm of Full Scale
- Temperature Option Available
- Best Accuracy: ± 0.015 ppm of Reading
- Wide Range of Ratios: 0.1:1 ~ 100:1
- Extended Low End Range Down to 1 μΩ with Currents Up to 10,000 A
- Range Extenders in 150 A Increments with Built-In Power Supplies and Switching
- Fully Programmable IEEE 488.2
- ♦ BridgeWorks[™] Data Acquisition Software
- Unique Calibration Support Strategy
- Complete Measurement Systems Available

GUILDLINE INSTRUMENTS 6622A SERIES introduces new design concepts and the best in measurement uncertainties for Direct Current Comparator (DCC) Resistance Bridges manufactured by anyone today. Unique innovations in 6622A design and modularity means users no longer have to decide what Bridge satisfies current requirements as well as guess as to what Bridge would meet future requirements. Optional modules allow for normal, high ohms, and low ohms measurements without having to purchase multiple bridges.

The 6622A Series modular design allows you to buy what is required today with existing budgets, and when workload requirements change, simply expand your bridge to meet these requirements without any loss of your original investment! Modular design provides a **ONE BRIDGE** solution reducing life cycle costs not only for equipment support, but also for software development and technician training. Modular design provides the perfect solution for current and future needs, whether you need secondary uncertainties or a Primary Laboratory Standard.

The concept and implementation is easy. You can start with the low-cost 6622A Base DCC Bridge with uncertainties down to 0.1 ppm and measurement range to 100 k Ω . Workload requirements demand higher measurement range? Then start with the eXtended Range (XR) model with its measurement range to 100 M Ω . You can move to better uncertainties with an eXtended Performance (XP) or eXtended Performance & Range (XPR) models. You can even start with or upgrade to the world's leading High Voltage Model (HV) with uncertainties down to 0.02 ppm and a measurement range of 1 G Ω and with built-in voltages to 1000 Vdc.

The 6622A Series Provides the Best Measurement Specifications, Widest Range of Options, and Most Innovative Modular Design of Any Commercially Available DCC Bridge!

If you already own the base model, Guildline can upgrade this unit to provide extended range, extended performance or even improve both range and uncertainties. The choices are yours and designed to meet your workload, not ours! Best of all, your current software programs will work and the menus will be the same, thus dramatically reducing learning curves and training requirements. Ongoing operating costs are also dramatically reduced because a **ONE BRIDGE** series offers reduced support costs when the time comes for calibration.

Available Bridge expansions for all models include external current range extenders at 3 A and 10 A and at 150 A increments up to 10,000 A, internal voltages to 1000 Vdc, and complete temperature capability. Or simply invest in the best from the beginning!

The unique design is based on over 30 years of knowledge and experience in building DCC Bridges. **Innovation abounds** and your **Investment is protected.** When you buy any 6622A Series Bridge it's as if you know them all. Menu operation, measurement setup, measurement operation and software are identical among all models. When you want extended range or enhanced performance – you still have only **ONE BRIDGE to support for calibration**. Just look at the **models and expansion paths** available for you with the 6622A Direct Current Comparator **ONE BRIDGE** Series.

6622A Series – Models and Expansion Paths

You can start with our very competitively priced 6622A



 Base
 unit.
 The

 6622A
 "Base"
 unit

 provides
 an

 outstanding

 measurement
 range

 of 0.001 Ω to 100 kΩ.

with b 0.03 p meet

with best uncertainties starting at 0.03 ppm. A perfect solution to meet demanding workloads and laboratory budgets. Learn only One

Menu and One Software package for all Bridges in this Series.

Or start out with the **6622A-XP** (eXtended Performance) Model. This model has the same measurement range as the 6622A Base Model...however the uncertainties of the



measurement ranges are significantly enhanced. If you already own the 6622A and now your workload demands



workload demands better uncertainties, simply return the unit to Guildline and we can expand the 6622A to a 6622A-XP. Instrument control and internal

menus will be the same, and your software procedures will still work – the same instrument operation and calibration support but with the improved uncertainties you need!

The newest addition to our line is the 6622A-e**X**tended **P**erformance **S**pecial accuracy model. This bridge can be upgraded from our Base and XP series only and does not have the extended range available. This bridge was the



8848800

This bridge was the result of many NMI's asking for the best uncertainties

available. Guildline responded with the XPS model. Specially

calibrated for 1:1 ratios expect better than 0.015 ppm in the mid-range of this bridge. Note that this is the only bridge that

cannot be fitted with the Temperature option.

Need a higher measurement range? Move up to our

model 6622A-XR (eXtended Range). This laboratory standard provides outstanding working measurement range

of 0.001 Ω all the way to 100 M Ω and with an internal 100 V supply. The best part is **No-Buyers Remorse**. If you had previously



purchased a 6622A-Base Model, and now your workload has evolved to higher values, simply send the instrument back to Guildline and we will **enhance your 6622A to a** 6622A-XR at a very attractive price.

Need Primary Laboratory Performance? Our **6622A-XPR** has both the **eXtended Performance and Range.** Primary

Level Performance at a secondary pricing structure and you can expand from any previous 6622A Series model. With 0.03 ppm







work-horse. As an added bonus, all DCC Bridges within this series come complete with BridgeWorks[™] Software.

WHY NOT EQUIP YOUR LABORATORY WITH THE BEST! Our 6622A-HV (High Voltage) model has the highest measurement range @1 G Ω , the highest voltage @ 1000Vdc and at 0.02 ppm this standard provides the ultimate measurement capabilities of any DCC Bridge available

today. You can expand from the 6622A-Base to the 6622A-XR or the 6622A-XP and from all of these bridge

models to the 6622A-XPR and the 6622A-HV. Innovation, performance, and investment protection delivered with the **ultimate in expansion flexibility!**







6622A Series – The Best in Engineering Design, and Innovation

An easy-to-use, front panel **menu system is common to all models** eliminating in-depth operator learning requirements. **IEEE 488.2** is standard on all models with the universally recognized **Standard Code Programmable Interface (SCPI)** based commands incorporated as the programming language of choice. You can have a rack or bench mount model and even have your choice of **front or rear terminals**. Your requirements, your needs - one family of instruments.

All 6622A Bridges now provide a full 10^{1/2} digits of resolution and the ability to **graphical see** the data (trending). You can have the data presented in a **summary or detailed format** right on the Bridge Screen or available via PC Base BridgeWorks Software. Measurement and **Uncertainty Analysis** you need as a Metrologist or to meet the requirements of ISO Accreditation.






Examples of Actual 6622A Display Pictures Taken at Trade Shows - Note Std Dev is in ppm showing **ppb performance**!

Every effort has been taken in the 6622A Series design to reduce noise and error. **Thermal EMF effects are eliminated** by automatic current reversal. The **unique architecture** of the bridge and its **control algorithm** further removes gain and offset errors in the **nanovolt balance detector** and the **precision toroid**. The end results are shown by **long term accuracy and linearity** without the need for routine, frequent verification tests or calibrations.

The 6622A bridges can be used in either a **fixed or automatic reversal rate** mode of operation. In fixed reversal rate mode, **automatic current polarity reversal** is programmable, updating measurements from every 2 seconds to 14 minutes. Unique computerized measurement mode provides automatic reversal rates, optimizing the polarity reversal rate. In resistance measurement the **fastest measurement speed** is achieved while maintaining required measurement uncertainty. In temperature applications, this feature makes it possible to **track fast changing temperatures**.

And it's not just the modularity that makes the 6622A Series unique and the best ONE BRIDGE solution offered today. Historical



100:1 Transfer (10 kΩ to 1 MΩ)

limitations of 13:1 ratio ranges have been eliminated. With new resistance **measurement ratios from 0.001:1 up to 100:1**, the 6622A series allows the ultimate **flexibility in choosing standards**.

Just take a look at results from using a **10 k\Omega Resistance Standard to 1 MΩ UUT** (Unit Under Test) measurement in a typical 100:1 measurement. The results are good – very good. Wider measurement ratios equate to fewer standards required to perform measurements. In fact, the 6622A series can be used for measurements from **1 μΩ to 100 MΩ** with **just 4 (four) Resistance Standards required.**

Another advantage is that **temperature stabilized resistance standards** (both oil based and air based) which have **very-low temperature coefficients** can now be used to characterize high value resistors (which typically have high temperature coefficients). For

example, you can now use a 100 k Ω Resistance Standard (Rs) from an oil bath to verify Rx values up to 10 M Ω . If you were to examine a typical measurement uncertainty workup, **measurement uncertainties** due to your resistance standard temperature coefficients are practically eliminated.

The 6622A Series, when used with the **Guildline Instruments Model 6634A or Model 6636 Temperature Stabilized Resistance Standards,** effectively **eliminate errors** due to the affects of temperature environment, even when used in a calibration laboratory environment of 23 °C @ \pm 3 °C.

6622A BridgeWorks Software

Not only does Guildline provide unique DCC Bridge hardware, but we offer complete new solutions for software as well. The software program called **BridgeWorks** is now provided for setup, control, measurements, and reporting. BridgeWorks is provided free with any of the Bridges in the 6622A Series. **Optional BridgeWorks plugins** are available to expand BridgeWorks functionality. Users can always **upgrade** to BridgeWorks should the requirement arise in the future. BridgeWorks, is the **upgrade path for current ResCal** users.

BridgeWorks software is extremely powerful, yet **straight forward and user friendly**. The software comes with all of the useful and convenient features commonly found in **window based** commercial software programs. **On-line context help** is available

to provide added assistance in understanding the functions of the software. BridgeWorks was **developed in LabVIEW**© offering direct compatibility to all National Instruments GPIB interfaces. These interfaces come in a wide variety of connection options to your PC such as **USB, FireWire, Ethernet, PCI, PCMCIA, RS232/485**, and more. Guildline can even provide a complete Resistance Measurement System with the 6622A Series **ONE BRIDGE** solution by adding Resistance Standards, Scanners, Range Extenders and software. This system is integrated, verified and tested in a rack a little more than 36" high. **Complete turnkey solutions.**

Test Configuration - untitled	I.SEQ				×
Scanner Setup		Edit Scanner Chan	nel No. 쉬 🛛 2 [Load Edi	Clear
C:\Program Files\Bridge\Vorks\10	kohm template.RES	_			
Fest Setup Add T	o End	Edit Test No. 🕤	1 Duplicate	Insert Sugge	est Clear
Rx Channel $\frac{2}{7}$ compared to	Rs Channel 🖒 🚺 at	() 1.000 ()	mA in Of	nms, with the referer	nce as () Rs
This Reversal Rate is () 60 s				a Threshold of 쉬	0.000 ppm.
Stop the test if a Target Deviation					
Start Process 🕣 in 🗧	1 sec.	onds from now with	a Between Test (Delay of 💮	1 (s).
Environment O 6623A	20 New	/ Open	Save	Cancel	Start
has been set 🤎 🛛 Ratio x 🗊	20 New	Upen open	Save	Cancer	Statt

For a **complete, automated resistance** or **temperature** measuring system, a 6622A Series bridge can be used with Guildline's 6664C Low Thermal Scanners and Guildline's 6634A Temperature Stabilized Resistance Standards. When the Bridge is used with

IT	5-90 Coef	ficients Repo	rt
Fixed P BT(In)	oint Measurements NaN	Coefficients	
RT(Zn)	NaN	a 1.247797987E+0 b 1.145083660E-1	
RT(AI) RT(Ga)	NaN NaN	○ 0.000000000E+0 d 0.00000000E+0	
RT(Ag)	NaN	Range 4 -189.35 to (10
RT(Ar) RT(Sn)	2.158975000E+1 NaN	RTPW 1.000000000E	-
RT(Hg)	8.441421100E+1		
	imber 259865 umber 1683	Uncertainty Cal Date 2006/07/15	ppm


a Guildline low **thermal matrix scanner**, the software can turn the bridge into a **multiple-channel** calibration and measurement system. Timed, sequenced single or multiple tests can be initiated while the bridge is unattended. All user **definable test variables**, such as excitation current, reversal rate etc can be **programmed on a per test basis**, giving the **users full control and flexibility** in conducting well designed experiments. Additionally, internal utilities reside within the software to enhance and **simplify the calibration of the 6622A** Series DCC Bridge by using the Guildline 6634A Series of Temperature Stabilized Resistance Standards.

BridgeWorks Software provides comprehensive graphic display, math functions and trend analysis. Data can be easily exported to MS-Excel®, Crystal Reports® and in HTML

format. All reports generated conform to traceability requirements of ISO-17025. BridgeWorks also provides **additional temperature capability** for those metrologists requiring this additional capability.

Report - 5700.FLK	X	
Fluke 570	0A Report	Save Print Close
Element	Values (ohms)	Uncertainties (ppm)
1ohm	1.000009566E+0	2.159
1.9ohm	1.899992171E+0	2.152
10ohm	9.999631792E+0	2.151
19ohm	1.899969515E+1	2.150
100ohm	9.999672844E+1	2.150
190ohm	1.899925862E+2	2.150
1kohm	9.999966388E+2	2.158
1.9kohm	1.900003481E+3	2.150
10kohm	9.999944887E+3	2.106
19kohm	1.899915655E+4	2.106
100kohm	9.999890021E+4	2.005
190kohm	1.899989581E+5	2.001
1Mohm	9.999956625E+5	2.416

BridgeWorks enhances resistance capabilities on other laboratory standards through the use of plugins and utilities. These optional utilities



include **calibration routines** for High End Calibrators such as the **Fluke 5700A and 5720A Series**, Agilent 3458A Long Scale DMM's and others. **Each output** value is calibrated by **direct** ratio transfer to the working set resistors, not calculated as by artifact calibration.

> There is even a utility for the **automated calibration of decade boxes**. This utility allows for direct calibration up to an 8-dial decade box spanning the full system measurement range. The utility is designed to **measure the absolute resistance value of each decade** box step and determine if the value is within the nominal tolerance specification. The utility incorporates a provision to **allow for trimming** of an adjustable decade box such as the ESI 925 and **supports both direct reading and standard decade boxes**.

6622A Series Specifications

Note: The 6622A-Base, 6622A-XP and 6622A-XPS models are limited to a maximum of 100 k Ω with a maximum Rs (Resistance Standard) of 10 k Ω . Because of the unique variable ratios available on all models, it is possible to measure UUT's with a variety of Rs Standards. For example, a 10 k Ω UUT could be measured with a 100 Ω , 1 k Ω and 10 k Ω Resistance Standard (Rs). To determine the measurement uncertainty due to the bridge, simply look at the Rs you are using, and then go to the appropriate UUT Sub range.

				Low Ohms Ratios ¹						
6622	2/4	-B ASE		Rs	1Ω ►	± 0.8 ppm			± 0.7 ppm	
				Nominal R	ATIO 🕨	0.0	01:1		0.01:1	
XP Range:	1 m	Ω ◀ ► 100 kΩ		Actual R	ATIO 🕨	0.8m >	Rx < 0.008		0.008 > Rx < 0.08	
INTERCHANGE ¹ SPECIFICATION		Resistance Standard		3 Үе.	ar R	ΑΤΙΟ S	PECIFIC	АТ	IONS ²	
0.8 > Rx < 6.3	•	ACTUAL RATIO		0.08 > Rx < 0.8	0.8	> Rx < 6.3	6.3 > Rx < 13.4		13.4 > Rx < 107.5	
1:1	•	Nominal Ratio		0.1 : 1		1:1	1:1 10:1		100:1	
± 0.03 ppm	•	1Ω		± 0.6 ppm	± C	.1 ppm	± 0.1 ppm		± 0.1 ppm	
± 0.03 ppm	◄	10 Ω		± 0.6 ppm	± C	.1 ppm	± 0.1 ppr	n	± 0.1 ppm	
± 0.03 ppm	•	100 Ω		± 0.6 ppm	± 0	.1 ppm	± 0.1 ppr	n	± 0.3 ppm	
± 0.03 ppm	•	1 kΩ	▲	± 0.6 ppm	± C	.1 ppm	± 0.1 ppr	n	± 0.8 ppm	
± 0.05 ppm		10 kΩ		± 0.6 ppm	± 0	.1 ppm	± 0.2 ppr	n	[XR MODEL]	

	_					Low Oh	ms Ratios ¹			
662	2/	A-XR		Rs	1Ω ►	± 0.8	3 ppm		± 0.7 ppm	
				Nominal F	Ratio 🕨	0.0	01:1		0.01:1	
Base Range:	:1 m	nΩ ⊲ ► 100 MΩ		Actual F	Ratio 🕨	0.8m >	Rx < 0.008		0.008 > Rx < 0.08	
INTERCHANGE ¹ SPECIFICATION STANDARD				3 Үе	AR R	ΑΤΙΟ S	PECIFIC	АТ	IONS ²	
0.8 > Rx < 6.3		ACTUAL RATIO		0.08 > Rx < 0.8	0.8	> Rx < 6.3	6.3 > Rx < 13	3.4	13.4 > Rx < 107.5	
1:1	•	Nominal Ratio	▲	0.1:1		1:1	10:1		100:1	
± 0.03 ppm		1Ω	▲	± 0.6 ppm	± 0	.1 ppm	± 0.1 ppm		± 0.1 ppm	
± 0.03 ppm	◀	10 Ω		± 0.6 ppm	± 0	.1 ppm	± 0.1 ppm		± 0.1 ppm	
± 0.03 ppm		100 Ω		± 0.6 ppm	± 0	.1 ppm	± 0.1 ppr	n	± 0.3 ppm	
± 0.03 ppm	•	1 kΩ	▲	± 0.6 ppm	± 0	.1 ppm	± 0.1 ppr	n	± 0.8 ppm	
± 0.05 ppm		10 kΩ		± 0.6 ppm	± 0	.1 ppm	± 0.2 ppr	n	± 3 ppm	
± 0.15 ppm	•	100 kΩ		± 1 ppm	± 0	.3 ppm	ppm ± 0.5 ppm		± 6 ppm	
± 0.25 ppm	•	1 ΜΩ	▲	±2.5 ppm ± 0		.6 ppm ± 0.8 ppm		n	± 8 ppm	
± 2.0 ppm	•	10 MΩ		± 8 ppm	±	4 ppm	±8 ppm	1	[HV MODEL]	

					Low Oh	ms Ratios ¹			
662	2	A-XP	Rs	1Ω ►	± 0.1	7 ppm	7 ppm ± 0.6 ppm		
			Nominal R	ATIO 🕨	0.0	01:1		0.01:1	
XP Range:	1 m	Ω ◀ ► 100 kΩ	Actual R	ATIO 🕨	0.8m >	Rx < 0.008		0.008 > Rx < 0.08	
INTERCHANGE ¹ SPECIFICATION		RESISTANCE STANDARD	3 Үе.	AR R	ΑΤΙΟ S	PECIFIC	АТ	I O N S ²	
0.8 > Rx < 6.3	◄	ACTUAL RATIO	0.08 > Rx < 0.8	0.8	> Rx < 6.3	6.3 > Rx < 13.4		13.4 > Rx < 107.5	
1:1	◄	Nominal Ratio	0.1 : 1		1:1	10:1		100:1	
± 0.02 ppm	◄	1Ω	± 0.4 ppm	± 0.	05 ppm	± 0.05 ppm		± 0.1 ppm	
± 0.02 ppm	◄	10 Ω	± 0.4 ppm	± 0.	05 ppm	± 0.05 pp	m	± 0.1 ppm	
± 0.02 ppm	◄	100 Ω	± 0.4 ppm	± 0.	05 ppm	± 0.05 pp	m	± 0.3 ppm	
± 0.02 ppm	▼	1 kΩ	± 0.4 ppm	± 0.	05 ppm	± 0.05 pp	m	± 0.8 ppm	
± 0.03 ppm	▼	10 kΩ	± 0.4 ppm	± 0.	05 ppm	± 0.15 pp	m	[XPR MODEL]	

						Low Oh	ms Ratios ¹		
6622		\-XPR		Rs	1Ω ►	± 0.7 ppm		± 0.6 ppm	
				Nominal R	RATIO 🕨	0.0	01:1		0.01:1
XPR Range:	1 m	nΩ ◀ ► 100 MΩ		Actual R	Ratio 🕨	0.8m >	Rx < 0.008		0.008 > Rx < 0.08
INTERCHANGE ¹ SPECIFICATION STANDARD				3 Үе	AR R	ΑΤΙΟ S	PECIFIC	АТ	IONS ²
0.8 > Rx < 6.3	•	ACTUAL RATIO	►	0.08 > Rx < 0.8	0.8 > Rx < 6.3		6.3 > Rx < 13.4		13.4 > Rx < 107.5
1:1	•	Nominal Ratio	►	0.1 : 1	1:1		10:1		100:1
± 0.02 ppm	•	1Ω	►	± 0.4 ppm	± 0.	05 ppm	± 0.05 ppm		± 0.1 ppm
± 0.02 ppm	•	10 Ω	►	± 0.4 ppm	± 0.	05 ppm	± 0.05 ppm		± 0.1 ppm
± 0.02 ppm	•	100 Ω	►	± 0.4 ppm	± 0.	05 ppm	± 0.05 pp	m	± 0.3 ppm
± 0.02 ppm	•	1 kΩ	►	± 0.4 ppm	± 0.	05 ppm	± 0.05 pp	m	± 0.8 ppm
± 0.03 ppm	•	10 kΩ	►	± 0.4 ppm	± 0.	05 ppm	± 0.15 pp	m	± 3 ppm
± 0.1 ppm	◄	100 kΩ	►	± 0.7 ppm	± 0.2 ppr		± 0.3 ppm		± 6 ppm
± 0.2 ppm	◄	1 ΜΩ	►	±1.5 ppm	±1.5 ppm ± 0.4 p		4 ppm ± 0.6 ppn		± 8 ppm
± 1.5 ppm	•	10 MΩ		± 8 ppm	± 2	.5 ppm	±4 ppm		[HV MODEL]

						Low Oh	ms Ratios ¹			
6622		\-XPS		Rs	1Ω ►	± 0.1	7 ppm		± 0.6 ppm	
				Nominal R	ATIO 🕨	0.0	01:1		0.01:1	
XPS Range:	:1 m	nΩ ◀ ► 100 kΩ		Actual R	atio 🕨	0.8m >	Rx < 0.008		0.008 > Rx < 0.08	
INTERCHANGE ¹ SPECIFICATION		Resistance Standard		3 Үе.	AR R	ΑΤΙΟ S	PECIFIC	АТ	IONS ²	
0.8 > Rx < 6.3	◄	ACTUAL RATIO	▲	0.08 > Rx < 0.8	0.8 > Rx < 6.3		6.3 > Rx < 13	3.4	13.4 > Rx < 107.5	
1:1	◄	Nominal Ratio		0.1 : 1		1:1	:1 10:1		100:1	
± 0.015 ppm	▼	1Ω		± 0.4 ppm	± 0	.02ppm	± 0.03 ppm		± 0.1 ppm	
± 0.015 ppm	▼	10 Ω	◀	± 0.4 ppm	± 0.	02 ppm	± 0.03 pp	m	± 0.1 ppm	
± 0.015 ppm	◄	100 Ω	▲	± 0.4 ppm	± 0.	02 ppm	± 0.03 pp	m	± 0.3 ppm	
± 0.015 ppm	▼	1 kΩ		± 0.4 ppm ± 0.		02 ppm	± 0.03 ppm		± 0.8 ppm	
± 0.03 ppm	◄	10 kΩ		± 0.4 ppm	± 0.	05 ppm	± 0.15 pp	m	[HV MODEL]	

						Low Oh	ms Ratios ¹			
662	2	A-HV		Rs	ΙΩ ►	± 0.1	7 ppm		± 0.6 ppm	
				Nominal R	ATIO 🕨	0.0	001:1		0.01:1	
HV Range	:1r	mΩ ◀ ▶ 1 GΩ		Actual R	ATIO 🕨	0.8m >	Rx < 0.008		0.008 > Rx < 0.08	
INTERCHANGE ¹ SPECIFICATION STANDARD				3 Үе	3 YEAR RATIO SPECIFICATIONS ²					
0.8 > Rx < 6.3	◄	ACTUAL RATIO		0.08 > Rx < 0.8	0.8	> Rx < 6.3	6.3 > Rx < 13	3.4	13.4 > Rx < 107.5	
1:1	◄	Nominal Ratio		0.1 : 1		1:1	10:1		100:1	
± 0.02 ppm	◄	1Ω		± 0.4 ppm	± 0	.04ppm	± 0.04 ppm		± 0.1 ppm	
± 0.02 ppm	◄	10 Ω		± 0.4 ppm	± 0.	.04 ppm	± 0.04 ppm		± 0.1 ppm	
± 0.02 ppm	◄	100 Ω		± 0.4 ppm	± 0.	.04 ppm	± 0.04 ppm		± 0.3 ppm	
± 0.02 ppm	◄	1 kΩ		± 0.4 ppm	± 0.	.04 ppm	± 0.04 pp	m	± 0.8 ppm	
± 0.03 ppm	◄	10 kΩ		± 0.4 ppm	± 0.	.05 ppm	± 0.15 pp	m	± 3 ppm	
± 0.1 ppm	◄	100 kΩ		± 0.7 ppm	± 0	.2 ppm	± 0.3 ppr	n	± 6 ppm	
± 0.2 ppm	◄	1 ΜΩ		±1.5 ppm ± 0.		.4 ppm	± 0.6 ppm		± 8 ppm	
± 0.7 ppm	◄	10 MΩ		±4 ppm ± 1.		.0 ppm	± 2 ppm		[MODEL 6530]	
± 2.5 ppm	▼	100 MΩ		± 8 ppm	± 3	.5 ppm	±6ppm		[MODEL 6530]	

1 - Interchange specification (i.e. sometimes referred to as a self-calibration) and Low Ohms Ratio specifications - refer to 6622A Manual for additional information about Low Ohms and Interchange specifications.

2 - 3 Year Calibration interval with annual performance verification (automated).

3 - Specifications are based on 10 mW R_s power dissipation or the maximum current in Rs or the limit of 6622A output and temperature of 23°C ±3°C.

4 - Ratio uncertainties Less than 0.08:1 for Rs 10 Ohm and below are calculated using 6623A Range Extender Series with the 6622A Series Bridge.

5 - Lowest possible R_x Ratio is defined as $R_{xlow} = R_s x$.08 and Maximum possible R_x Ratio is determined by $R_{xhigh} = R_s x$ 107.5.

6 - Maximum Upper Range is limited to 134 k Ω for 6622A, 6622A-XP and 6622A-XPS with the maximum Rs allowed as 10 k Ω .

7 - Maximum Upper Range is limited to 134 M Ω for 6622A-XR and 6622A-XPR with the maximum Rs allowed as 10 M Ω .

8 - Maximum Upper Range is limited to 1.34 G Ω for 6622A-HV with the maximum Rs allowed as 100M Ω based on 1000 V.

	6622A Series General Specifications							
Linearity				\pm 0.01 ppm of full scale (Full scale defined as 13.4:1 and 100:1)				
Display resolution (p	opm)			Selectable (Progr	rammable)	from 0.0001 pp	om to 10 ppm	
Temperature Coeffic	cient			0.01 ppm/°C of re	eading			
Automatic current re	eversal rate (in sec	conds) s		4 sec to 1637 sec	's programi	mable, increme	ent of 1 second	
Fastest Measuremer	nt Sample Rate			2 seconds				
Communication				IEEE 488.2 (SCPI E	Based Lang	uage Instructio	ins)	
Test current (for	Usable range (±	30V) compliance) (A	۹) (10 μA ~ 150 mA (extension to 10,000A available)				
measurement to 100kΩ)		Resolution (µA	۹)	1 μΑ				
	Accuracy [e	rror(ppm) + offset(A))]	±100 ppm ± 10 μ	ιA			
Test voltage (for	V _{DC} Range (±	1mA compliance)	0 ~	~ 100 Vdc (XR and	XPR mode	s). HV Model h	nas 0 ~ 1000 Vdc	
measurement		Resolution (V)	1 V	1 V for Bridges with 100 Volt Module, 256 bit for 1000 Volt Model (\approx 4V)				
above 100kΩ)		Accuracy error (%)	±Ο	$\pm 0.2\%$ of full scale voltage output				
Bridge Operating Te	mperature to Full	Specifications		23°C ± 3°C		73°F ± 5°F		
Bridge Maximum Op	perating Range (<	50% RH)		+18°C to +25	5°C	+65	+65°F to +82°F	
Bridge Temperature	Storage Range			-20°C to +60	°C	-4°F	⁼ to +140°F	
Power Requirement	S	VAC: 100V, 120V, 220	0V and 240V \pm 10% / 50 or 60Hz \pm 5%, 200VA					
	Dimensions (Widt	h x Height x Depth)			Weight			
440 mm x 200 mm x 465 mm 17.3" x 7.				x 18.3″ 27 kg		59.5 lbs		

NEW - 6623A-Series of Modular Range Extenders

Range Extenders allow DCC Bridges to measure "lower" resistance values (including current shunts) at higher current. Using proprietary technologies, Guildline engineers have again provided our customers with the most value and flexibility in expanding their **shunt measurement** capability. For calibration at higher currents, additional range extenders **can be cascaded** by the 6622A to expand the maximum allowable current for **improved calibration uncertainty.** The range extender carries out polarity reversal automatically, at user selected

intervals. Standard models are 6623A-3, 6623A-10, 6623A-150, 6623A-300, 6623A-450, 6623A-600 6623A-1000, 6623A-2000 and 6623A-3000, 6623A-





6000, 6623A-10000, each with built-in current source with maximum currents of **3A**, **10A**, **150A**, **300A**, **450A**, **600A**, **1000A**, **2000A**, **3000A**, **6000A**, **10,000A** respectively. Pictures of the rear connections for the 300 Ampere (top right) and 3000 Ampere (left) models are shown.

Models with other maximum current levels are available in multiples of 150A. If you buy lower current models such as the 150A, and now need 900A, no worries. **Just return the unit to Guildline** and we will upgrade it to a 900A model for you. Your Investment is protected. NOTE that **NO external power supplies**, **NO external mechanical switches**, and **NO compressed air are required** for operation. This results in dramatically reducing the purchase/installation cost, as well as ongoing training, calibration support, and operating costs. The 6622A-150 and 6623A-300 can both be operated from **a single-phase 120VAC input** and do **NOT** require a dedicated 3 phase circuit.

For More information about the 6623A Range Extenders and Specifications, Please refer to the 6623A Series Datasheet.

NEW - 6622A "T" OPTION FOR THERMOMETRY APPLICATIONS

Using the latest DC current comparator technology, Guildline model 6622A Series are very well suited for temperature calibration and their measurement ranges are designed for thermometry. DCC bridges have inherently better noise immunity to external electromagnetic and mechanical noise. Measurements are conducted in true four-terminal mode so long test leads can be used. Since excitation current is DC, reactance introduced by the probe and probe leads does not affect measurement accuracy. Thermal EMF is eliminated by periodic polarity reversal that is programmable by the user. The builtin, extremely stable current supply permits selection of output currents between 20µA and 150mA to satisfy a wide range of sensitivity requirements. Root square values can be conveniently chosen from the instrument front panel or via software. Temperature conversion and display is done on the front panel, or on a PC using the BridgeWorks-C software

All 6622A models can be expanded to address temperature requirements without the need for a separate thermometry bridge, separate software, or manual calculations. The menu operation and calculations are done internally via firmware and the results can be viewed on the front panel in ohms, °C, °F, and K. The menu also provides the ability to change Temperature Scales, display graphics, and control all parameters.



One of the **key features** of the temperature option is how the unit is calibrated. This option means that the 6622A is specifically tested at the lower currents (1 mA) found in thermometry and these offsets are stored separately from the Resistance calibration constants.

Not only does Guildline provide the temperature option for the bridge, but check out our full line of thermometry options including our **new 3210T Thermometry Auto-Switch**. This adaptor provides programmable and individual constant keep warm current to all SPRT's connected substantially reducing the time for calibration over the competition.

MAKING THE 6622A SERIES EVEN BETTER

Resistance verification of the 5700 values including the 1.9X Values.

Guildline provides a variety of standards to support the 6622A Series of Bridges. For the ultimate in ease of use and wide temperature operating environment, look at our 6634A Temperature



Controlled Resistance Standards. These resistance standards are a rack or bench mount unit with up to 10resistance values. The values are in a shielded, self contained 30°C temperature environment and



usable in a laboratory environment of $23^{\circ}C \pm 5^{\circ}C$. This series is extended in high values up to 100 T Ω by our model 6636. No more need for oil baths. For the **best in** air resistances see our 9334A, 9336 and 9337 Series of Air Resistance Standards.

For multi-channel operation look at our 6664C Scanners. These 8 or 16 Ouad channel scanners can handle up to 2 A of current or voltages up to 1000Vdc. You can stack up to four scanners as needed with a total of 64 channels accessible by BridgeWorks Software.





For the best Unit Under Test (UUT) environmental control Guildline produces the 5030 Series of Precision Air Baths. This series of programmable Air Baths not only maintain an ultra stable 0.03°C

environment but also provide EMI and EMF Shielding within the high quality Stainless Steel Chamber. Dual Heaters/Coolers/Fans provide for operational redundancy and the unit is fully IEEE 488 programmable. Control Resolution is a 0.001°C and a second channel is available for a second user programmable sensor that can be read directly on the front panel. This bath incorporates an extensive Metrology based menu operation.

And Guildline's innovation continues with the 66252 DMM Switch. The purpose of this switch is to electrically isolate the Bridge, when using Resistance Standards that are

connected to a scanner. This usefulness can be seen using a 5700 Calibrator as an example. The user is able to connect resistance standards that are on a scanner channel to Artifact calibrate the Calibrator and then simply switch over and run the complete



Guildline also provides full system solutions and full system integration. Need a base system with one scanner and a resistance standard in a rack? Not a problem. Need a 6622A-XPR with 48 channels, Resistance Standards and with Range Extension to 900 As? We can do it! In fact, Guildline has produced over one hundred 6622A based systems complete with Range Extension, Multi-Channel Scanners, and Resistance Standards all in a 36" rack. Units were supplied with all hardware, software installed, tested and verified. Need the **ultimate resistance measurement** in a single stand solution? Combine any one of the 6622A Series Bridges with a 6634A Temperature Stabilized Resistance Standard, a 150A to 600A Range Extender for low Ohm measurements, and a 6520 **Digital Programmable Teraohmmeter.** Start measuring from 1 $\mu\Omega$ all the way to **10 PΩ**. Just ask what **Guildline can make for you**.

VERIFICATION OF PERFORMANCE

Bridges are not self-calibrating. All Bridges must have an initial calibration done at time of manufacture, and subsequently must be verified or re-calibrated on a periodic time schedule. Competitors misleadingly state that their Bridges are self-calibrating but in reality their Bridges are calibrated the same way as all commercial bridges including Guildline's - via external resistance standards.

Historically the verification that a precision DCC Bridge is operating as per its last calibration was challenging. A Harmon type transfer standard was needed for the verification of a bridge's non 1:1 measurement ratios along with high technical skill levels. With the introduction of the 6622A multi-ratio bridge, the verification of performance can be carried out with ease. Frequent verification of the bridge performance can also provide insight into the bridge's short and long-term stability to improve user's confidence levels and uncertainties.


The 1:1 measurement ratio can be easily verified by interchange measurement tests using two stable standard resistors of same nominal values, as illustrated by the block diagram to the right. Bridge 1:1 measurement ratio error e_i (in ppm) is calculated using the following formula

$$e_i = (1/2) \cdot |R_1 \cdot R_2 - 1| \cdot 10^6$$

Non 1:1 measurement ratios, such as 10:1 and 100:1 ratios can be easily verified by closure measurement tests using three stable standard resistors, as illustrated by the block diagram to the right. Bridge non 1:1 measurement ratio error e_c (in ppm) is calculated using the following formula

$$e_{c} = (1/3) \cdot |R_{a} - R_{b} \cdot R_{c}| / R_{a} \cdot 10^{6}$$

Note: Resistance values in these block diagrams are only representative values and are selected for the illustration of methodology only.



WARRANTY

Over 58 Years of Guildline innovation in engineering and design. ONE BRIDGE providing complete expandability and flexibility that meets your current and future measurement needs. Options that satisfy real measurement needs and provide complete investment protection. How can you improve? Simple! Offer an industry leading 2-Year Warranty to show your confidence. All 6622A Series of DCC Bridges now come with a 2-year Warranty that covers both parts and labour.

Service and Support

Guildline is pleased to announce that they are **ISO 17025 Accredited**. We have the widest range of resistance accredited with a range of $1 \mu \Omega$ all the way to $10 P\Omega$. Whether you own a Guildline product and have other manufacturer's standards, call today and see what we can do for you.

	Ordering Information
Model	Specify One Of Following Models (Bench or Rack)*
6622A-B	Base Accuracy, Range 100 kΩ
6622A-XR	Base Accuracy, Extended Range to 100 M Ω
6622A-XP	Extended Performance, Range 100 k Ω
6622A-XPR	Extended Performance, Extended Range to 100 M Ω
6622A-XPS	Extended Performance Special, Range 100 k Ω
6622A-HV	Extended Performance, 1000 V, 1 G Ω Range
	*All Bridges include Calibration Certificate, Operator and Software manual, and one set of Rs/Rx Low Thermal Leads
/T	Add's Temperature Option to Bridge
/RC	Report of Calibration Available at Nominal Charge
/RT	Specifies Rear Terminals versus Front Terminals (Default)
SM6622A	Service Manual (Extra Charge)
6622A Series OP	TIONS
BridgeWorks-UPG	Upgrades BridgeWorks-R to BridgeWorks-C
/57XX UTL	BridgeWorks-C 57XX Resistance Calibration Utility
/3458 UTL	BridgeWorks-C 3458A Resistance Calibration Utility
/Controller	System Controller with IEEE and Software Integrated
IEEE-PCI	NI IEEE-488.2 Interface for a PCI slot (Win 9X/NT/ME)
IEEE-2m	NI IEEE-488.2 Interface cable, 2m double shielded
6634A-X	Temperature Stabilized Resistance Standard for 6622A Series
6623	100 A Direct Current Comparator Range Extender
66233	100 A Programmable Power Supply for 6623-100A
6623A-3	External 3A Range Extender for DCC Resistance Bridge
6623A-150	External 150A Range Extender for DCC Resistance Bridge
6623A-300	External 300A Range Extender for DCC Resistance Bridge
6623A-450	External 550A Range Extender for DCC Resistance Bridge
6623A-600	External 600A Range Extender for DCC Resistance Bridge
6623A-1000	External 1000A Range Extender for DCC Resistance Bridge
6623A-2000	External 2000A Range Extender for DCC Resistance Bridge
6623A-3000	External 3000A Range Extender for DCC Resistance Bridge
6623A-6000	External 6000A Range Extender for DCC Resistance Bridge
6623A-10000	External 10000A Range Extender for DCC Resistance Bridge
6664C	8 or 16 Channel, 2 A Low Thermal Scanner
3210	8 Channel Thermometry Adapter with Pre-Heat
6664A-12	SCW Lead pair with gold plated banana plugs, 2m in length
SCW/18-30	30 Meters Shielded, Copper, Low Thermal Wire 18 Gauge
Many other typ	es of test and communication leads and accessories are available.

GUILD*LINE* IS DISTRIBUTED BY:

6622A SERIES OF DCC BRIDGES

Guildline Instruments Limited 21 Gilroy Street, PO Box 99 Smiths Falls, Ontario Canada K7A 4S9 Phone: (613) 283-3000 Fax: (613) 283-6082 Web: www.guild*line.com* Email: sales@guild*line.com*

20149-00-85 Rev L COPYRIGHT © 2013-11-26 GUILDLINE Instruments Limited. All rights reserved. Specifications and Subject to change without notice.