NCC-3 Ceramic Cement



Strain Gage Cement

OTHER ACCESSORIES USED IN AN NCC-3 CEMENT INSTALLATION:

- CSM Degreaser or GC-6 Isopropyl Alcohol
- Silicon-Carbide Paper
- M-Prep Conditioner A
- M-Prep Neutralizer 5A
- GSP-1 Gauze Sponges
- GT-11 Camel Hair Brush
- SPT-1 Double Blade Spatula

DESCRIPTION

Single-part, silica-based ceramic cement for use with ZC-, ZWH-, and ZWN-Series high-temperature strain gages. Has superior bond strength to super-alloy materials, stainless steel, titanium, and other nonferrous alloys. **Not for use on mild steel.**





PARAMETERDETAILSOPERATING TEMPERATURE RANGE-452°F to +1470°F (-269° to +800°C°).ELONGATION CAPABILITIES0.5% at +75°F (+24°C).SHELF LIFE12 months after date of manufacture. Store at +75°F (+24°C).POT LIFE2 weeks after opening. Refer to product label for most recent information.TEMPERATURE COEFFICIENT OF EXPANSION7 ppm/°F (12.6 ppm/°C).Precoat: Air-dry 30 minutes at +75°F (+24°C). Bake at +200°F (+93°C) for 30 minutes. Increase temperature to 400°F (204°C) for 30 minutes. Increase temperature to 400°F (204°C) for 30 minutes. Increase temperature to 400°F (204°C) for 30 minutes.	CHARACTERISTICS	
ELONGATION CAPABILITIES 0.5% at +75°F (+24°C). SHELF LIFE 12 months after date of manufacture. Store at +75°F (+24°C). POT LIFE 2 weeks after opening. Refer to product label for most recent information. TEMPERATURE COEFFICIENT OF EXPANSION 7 ppm/°F (12.6 ppm/°C). Precoat: Air-dry 30 minutes at +75°F (+24°C). Bake at +200°F (+93°C) for 30 minutes. Increase temperature to 400°F (204°C) for 30 minutes. Increase temperature to 600°F (315°C) for 30 minutes. CURE REQUIREMENTS Final Cure: Air-dry 30 minutes at +75°F (+24°C). Bake at +200°F (+93°C) for 30 minutes.	PARAMETER	DETAILS
SHELF LIFE 12 months after date of manufacture. Store at +75°F (+24°C). POT LIFE 2 weeks after opening. Refer to product label for most recent information. TEMPERATURE COEFFICIENT OF EXPANSION 7 ppm/°F (12.6 ppm/°C). Precoat: Increase temperature to 400°F (204°C) for 30 minutes. Increase temperature to 400°F (204°C) for 30 minutes. Increase temperature to 600°F (315°C) for 30 minutes. CURE REQUIREMENTS Final Cure: Air-dry 30 minutes at +75°F (+24°C). Bake at +200°F (+93°C) for 30 minutes.	OPERATING TEMPERATURE RANGE	−452°F to +1470°F (−269° to +800°C°).
POT LIFE 2 weeks after opening. Refer to product label for most recent information. TEMPERATURE COEFFICIENT OF EXPANSION 7 ppm/°F (12.6 ppm/°C). Precoat: Air-dry 30 minutes at +75°F (+24°C). Bake at +200°F (+93°C) for 30 minutes. Increase temperature to 400°F (204°C) for 30 minutes. Increase temperature to 600°F (315°C) for 30 minutes. CURE REQUIREMENTS Final Cure: Air-dry 30 minutes at +75°F (+24°C). Bake at +200°F (+93°C) for 30 minutes.	ELONGATION CAPABILITIES	0.5% at +75°F (+24°C).
TEMPERATURE COEFFICIENT OF EXPANSION 7 ppm/°F (12.6 ppm/°C). Precoat: Air-dry 30 minutes at +75°F (+24°C). Bake at +200°F (+93°C) for 30 minutes. Increase temperature to 400°F (204°C) for 30 minutes. Increase temperature to 600°F (315°C) for 30 minutes. CURE REQUIREMENTS Final Cure: Air-dry 30 minutes at +75°F (+24°C). Bake at +200°F (+93°C) for 30 minutes.	SHELF LIFE	12 months after date of manufacture. Store at +75°F (+24°C).
OF EXPANSION Precoat: OF EXPANSION Precoat: Air-dry 30 minutes at +75°F (+24°C). Bake at +200°F (+93°C) for 30 minutes. Increase temperature to 400°F (204°C) for 30 minutes. Increase temperature to 600°F (315°C) for 30 minutes. CURE REQUIREMENTS Final Cure: Air-dry 30 minutes at +75°F (+24°C). Bake at +200°F (+93°C) for 30 minutes.	POT LIFE	2 weeks after opening. Refer to product label for most recent information.
Air-dry 30 minutes at +75°F (+24°C). Bake at +200°F (+93°C) for 30 minutes. Increase temperature to 400°F (204°C) for 30 minutes. Increase temperature to 600°F (315°C) for 30 minutes. CURE REQUIREMENTS Final Cure: Air-dry 30 minutes at +75°F (+24°C). Bake at +200°F (+93°C) for 30 minutes.		7 ppm/°F (12.6 ppm/°C).
	CURE REQUIREMENTS	Air-dry 30 minutes at +75°F (+24°C). Bake at +200°F (+93°C) for 30 minutes. Increase temperature to 400°F (204°C) for 30 minutes. Increase temperature to 600°F (315°C) for 30 minutes. Final Cure: Air-dry 30 minutes at +75°F (+24°C). Bake at +200°F (+93°C) for 30 minutes.

PACKAGING OPTION	
	1 bottle (1 oz/30 ml) cement



Disclaimer

ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "VPG"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

The product specifications do not expand or otherwise modify VPG's terms and conditions of purchase, including but not limited to, the warranty expressed therein.

VPG makes no warranty, representation or guarantee other than as set forth in the terms and conditions of purchase. To the maximum extent permitted by applicable law, VPG disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Information provided in datasheets and/or specifications may vary from actual results in different applications and performance may vary over time. Statements regarding the suitability of products for certain types of applications are based on VPG's knowledge of typical requirements that are often placed on VPG products. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. You should ensure you have the current version of the relevant information by contacting VPG prior to performing installation or use of the product, such as on our website at vpgsensors.com.

No license, express, implied, or otherwise, to any intellectual property rights is granted by this document, or by any conduct of VPG.

The products shown herein are not designed for use in life-saving or life-sustaining applications unless otherwise expressly indicated. Customers using or selling VPG products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify VPG for any damages arising or resulting from such use or sale. Please contact authorized VPG personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Copyright Vishay Precision Group, Inc., 2014. All rights reserved.